Measurement Data Wireless Communication System U-WAVE





Whatever your challenges are, Mitutoyo supports you from start to finish.

Mitutoyo is not only a manufacturer of top quality measuring products but one that also offers qualified support for the lifetime of the equipment, backed up by comprehensive services that ensure your staff can make the very best use of the investment.

Apart from the basics of calibration and repair, Mitutoyo offers product and metrology training, as well as IT support for the sophisticated software used in modern measuring technology. We can also design, build, test and deliver bespoke measuring solutions and even, if deemed cost-effective, take your critical measurement challenges in-house on a sub-contract basis.









Find additional product literature and our product catalogue

https://www.mitutoyo.co.jp/global.html

Our products are classified as regulated items under Japanese Foreign Exchange and Foreign Trade Law. Please consult us in advance if you wish to export our products to any other country. If the purchased product is exported, even though it is not a regulated item (Catch-All controls item), the customer service available for that product may be affected. If you have any questions, please consult your local Mitutoyo sales office.

Note: Product illustrations are without obligation. Product descriptions, in particular any and all technical specifications, are only binding when explicitly agreed upon. MITUTOYO and MiCAT are either registered trademarks or trademarks of Mitutoyo Corp. in Japan and/or other countries/regions.

Other product, company and brand names mentioned herein are for identification purposes only and may be the trademarks of their respective holders.

Mitutoyo

Mitutoyo Corporation

20-1, Sakado 1-Chome, Takatsu-ku, Kawasaki-shi, Kanagawa 213-8533, Japan T+81 (0) 44 813-8230 F+81 (0) 44 813-8231 https://www.mitutoyo.co.jp

What is the U-WAVE Series?

"U-WAVE", the measurement data wireless communication system, collects data in the inspection process swiftly and accurately, and increases a company's competitiveness based on detailed data analysis.

In addition, together with MeasurLink, "IoT of Quality Control envisioned by Mitutoyo" can be achieved.

Achieve Smart Measurement

Measurement Data Wireless Communication System

U-WAVE

This is a system that transmits data from Mitutoyo Digimatic gages to software such as Excel or Notepad via wireless communication. It saves time and eliminates misinput, helps achieve cost reductions and better efficiency while maintaining excellent operability.

See video from here

From a Digimatic gage connected with U-WAVE



Data is obtained via wireless communication and sent to commercial software such as Excel



Advantages of Introducing U-WAVE

Higher Efficiency

Data can be input by single button operation! Since there is no need for manual input misinput does not occur. Efficiency is greatly improved!

Centralized Data Management

Measurement data can be managed centrally!
"Visualization of quality" help prevent the generation of defective products!

Cost Reduction Effect

Easily connected to the Digimatic gage of currently in use!

A system configuration reducing the initial and running cost is possible.

* Some models of U-WAVE-

U-WAVE resolves measuring process issues!



Manual input of measurement data is inefficient and frequently generates misinput.



Issue

Loading measurement data via wireless is seen as desirable but justifying any high initial investment is difficult.



Issue

Since multiple operators use Digimatic gages, it takes a long time for data collection and Pass/fail judgment.



U-WAVE immediately transmits the measurement data to your PC. Misinput due to manual input can be eliminated, and therefore data reliability and operational efficiency is improved.

Solution

No high initial investment required because U-WAVE can be inexpensively connected to your existing Digimatic gages. No need to purchase replacements.

Solution


Up to 100 Digimatic gages can be registered to a single U-WAVE receiver on the PC side. The data is automatically entered separately in the Excel sheet. Therefore, data collection and Pass/fail judgment are easily performed.





Speedy and Reliable Data Collection and Pass/fail **Judgment Improves Manufacturing Competitiveness**

Higher Efficiency





Confirmation that data was successfully received.

Note: The buzzer sound is only available with the buzzer equipped model



- Normally received: green LED
- Buzzer sounds twice briefly

Dustproof and water resistant IP67 model

The water-proofed transmitter is resistant to water and dust.





Cordless enables freedom of movement

• Reception failed: red LED

Buzzer sounds once

Flexible layout of measurement site

Misinput generated by manual input is eliminated

Stable wireless communication



Centralized Data Management >

Operation in an Excel sheet

The data can be directly written into an Excel sheet.



Digitalization enables easy data collection and analysis

The measurement data from each process can be stored and managed centrally.



Multiple gages can be connected at the same time




Note:Receiver not necessary when using with Mitutoyo Bluetooth® U-WAVE fit

Cost Reduction Effect

If a Digimatic gage is damaged, operation can be continued using a different gage

The transmitter can be reconnected to a different



Connectable to any of your existing Digimatic gages

No need to buy a replacement if your tool is equipped with the Digimatic function.

Approximately 400,000 continuous data transmissions are possible


Just one CR2032 lithium battery provides power for about 400,000 data transmissions.


* When the battery is used with U-WAVE-TM/TC/T. The battery life is approx. one year under normal use when used with U-WAVE-TMB/TMC.

Type of U-WAVE

Convenient data collection tool and quality control software

• The following three types are currently available.







Function comparison table

	U-WAVE	U-WAVE fit*1	Bluetooth® U-WAVE fit*1				
Transmission method	Original <based iee<="" on="" td=""><td colspan="6">Original </td></based>	Original 					
Communication distance	Approx. 20 m	Approx. 20 m (line of sight)					
Connectible model	Digimatic gages	Digimatic calipers	and micrometers				
Dedicated application/ software		d with U-WAVE receiver) TPAK*2	U-WAVEPAK-BW U-WAVEPAK-BM U-WAVE Navi USB-ITPAK* ²				

^{*1} Please check the list of compatible models since the unit may not be attachable to some models.

^{*2} Please note that USB-ITPAK may not be recognized if your computer's OS build is old.

Typical Measuring Issues Solved

In combination with application software USB-ITPAK V2.1, better efficiency in quality assurance can be achieved.

Case Study

Case 1

Standard sequential measurement input

Issue

To record the measurement results, on a chart, from three points on a mass-produced product measured using two gages.

Solution

If you set the procedure of inputting data to the Excel sheet with USB-ITPAK V2.1, the measurement data is automatically entered.

*Please refer to "Option" at the bottom of this page.

Measure the workpiece dimensions, X and Y, with a micrometer.

Then, measure H with a caliper. Finally, visually check the appearance and judge OK or NG. Perform the above for 5 workpieces consecutively.






The designated table will be created by measuring and transmitting data for X and Y of 5 workpieces, measuring and transmitting data of H, and then entering the result of visual check.

Set the sequential measurement input order

Designate the Excel sheet, select the data loading range, loading order, and allocate the ID for each cell.

Measure X and Y for 5 workpieces with a micrometer.



Des	signated Exc	cel sheet	İ				
	Λ	R		D	E	E	

	Α	D			L	' '		
1	Setting	1	2	3	4	5		Input
2	Dimension X	10.025	10.033	9.964	10.031	10.046		range of —micrometer
3	Dimension Y	9.982	10.017	10.008	9.996	10.027	,	Input
4	Dimension H	29.97	30.02	30.07	29.96	30.04	4	_range of caliper
5	External Appearance	OK	OK	NG			4	_ Input range of visual
								judgment

Data will be input one by one in the registered order to the cells of the Excel sheet designated beforehand.

Case

Data input by multiple operators

Issue

To sort data into separate Excel sheets per Digimatic gage in the inspection process.

Solution

The data collected by multiple operators can be individually set to be input to the designated cells in the Excel sheet.

Input data of each Digimatic gage in order into the designated cells of the separate Excel sheet.




the same number of Excel sheets can be designated.

receiver and

nt) Designate the Excel sheet per Digimatic gage

Using USB-ITPAK, designate the Excel sheet per Digimatic gage. Then, same as the sequential measurement, select the data loading range, loading order, and allocate the IDs.



Multiple measurement data (via U-WAVE-TM/TC/T) can be sorted into the separate Excel sheets without requiring you to program macros.

Option

USB-ITPAK V2.1

Mitukoyo WiCAT The translation would receiving unlover USB dongle USB-ITPAK

A USB dongle must be connected to the PC running the software.

Measurement Data Collection Software

USB-ITPAK V2.1

USB-ITPAK V2.1 is optional software to be installed in the PC connected with U-WAVE-R. It enables setting up the procedure to input the measurement data received from U-WAVE-R to the Excel sheet and to achieve greater inspection efficiency and enhanced credibility.

The combined use with U-WAVE will improve the operational efficiency of the inspection work.

Best suited for recording data in mass-production inspections where the procedure is repeated every day.

■ Features of USB-ITPAK V2.1

- The measuring methods can be configured, such as sequential measurement, batch measurement, individual measurement and more.
- Data can be canceled by a single operation of the foot switch or function key.
- Input range can be specified per Digimatic gage, which reduces the chance of a misinput.
- Data input or cancellation can be instructed globally in multiple-point simultaneous measurement.
- The Excel sheet can be automatically called for data input.
- The cursor movement after data input can be set to enable automatic input.

Case Study

Case

Batch measurement using timer

Issue

To measure displacement using multiple Digimatic gages and automatically obtain data in a certain input interval.

Solution

Batch timer input is available using the USB-ITPAK batch measurement function and the optional timer input function.

Specify the interval for measuring the displacement of the workpiece and collect data at once.

Batch measurement with all the Digimatic gages

Data can be obtained globally by a foot switch operation.

Point Timer input option

Using USB-ITPAK, the data request interval can be set by hours, minutes,

(0.0 sec. to 24 hrs.).


		А	В	С	D	Е	F	G
	1	Displacement (1)	Displacement (2)	Displacement (3)	Displacement (4)	Displacement (5)	Displacement (6)	Measurement date/ time
After Food	2	0.281	0 162	0.121	0.051	0.011	-0.001	2013/4/1 7 30 00
After 5 sec. After 5 sec. After 5 sec.	3	0.279	0.152	0.133	0.064	0.018	-0.003	2013/4/1 7 30 05
	4	0.265	0 149	0 142	0 089	0.021	-0.007	2013/4/1 7 30 10
Arter 5 Sec.	5	■.		*****				
	6							

- To perform simultaneous measurement using U-WAVE, a special order software U-WAVEPAK (event drive)
- Since the data refresh interval of the event drive is fixed at 0.5 seconds, the setting range is from 0.5 seconds to 24 hours.

Point

Batch timer input

Data can be obtained at the desired interval using the timer input function in



Enables automatic

data load


Without operating

the send button of the

Digimatic gage, data can

be obtained automatically

from multiple Digimatic



"Button driven mode" and "Event driven mode"

Button driven mode

By pushing the Data button of digimatic gage/dedicated cable for U-WAVE/ connecting unit. indicated values can be transferred to the receiver.

Event driven mode

1) U-WAVE-TM/TC/T checks the displayed value of the Digimatic gage at 0.5 sec. intervals, and transfers data if the value is changed. 2) U-WAVE-R overwrites data

in the storage. 3) Sends data responding to

• The battery life of the U-WAVE-TM/TC/T is shortened (20 days in continuous operation). • U-WAVE is equipped with a function to avoid radio wave interference, and enables successful simultaneous data transmission of three U-WAVE-T units per U-WAVE-R. To perform simultaneous data transmission with more than three units of U-WAVE-T, an additional U-WAVE-R and set different frequencies (15 channels) to assure reliable wireless

the data request command.

"Event driven mode" is not available for U-WAVE-fit Bluetooth[®] within USB-ITPAK.

U-WAVE U-WAVE fit

Receiver

■ U-WAVE-R

- Receives measurement data and transmits to the PC via USB.
- Since USB bus power system is used, a battery or adapter is not required.
- The identification ID and frequency to be used can be set using supplied software U-WAVEPAK.
- The data load function to Excel, etc. is supplied as a standard accessory.

U-WAVE-R

PC (for storing data)

Data loaded to the PC via USB.

Transmitters

■ U-WAVE-TM/TC/T

- Transmits the measurement data displayed on the gage to U-WAVE-R.
- Compact, cable-less design provides a better fit with the Digimatic gage and better operability.

U-WAVE fit U-WAVE-TC **U-WAVE** fit U-WAVE-T U-WAVE-TM


Connecting unit/connecting cable

- A compact connecting unit connects the U-WAVE-TM/TC/T transmitter to the Digimatic gage.
- A dedicated cable connects the U-WAVE-T transmitter to the Digimatic gage.

Digimatic gages

Compatibility

- U-WAVE-TM/TC can be used with most of the calipers and micrometers equipped with the Digimatic output function.
- U-WAVE-T can be used with all the Digimatic gages equipped with the Digimatic output function.



Transmitters

U-WAVE fit

With functions and performance inherited from U-WAVE-T, a compact and thinner design provides a neater solution by eliminating cabling around the Digimatic gage and thus better operability!




U-WAVE-TM for micrometers and U-WAVE-TC for calipers are available, both the buzzer type and IP67 type. The buzzer type notifies the normal reception of data by LED and buzzer sound. The dust/water-proof IP67 type is designed for a harsh environment and as such is only equipped with LED notification of data reception.

Type of Transmission Unit

U-W/VE

This product successfully introduced U-WAVE to the market.







The buzzer type and IP67 type are available. The buzzer type notifies the normal reception of data by LED and buzzer sound. The IP67 type is designed for a harsh environment and as such is only equipped with LED notification of data reception.

■ Connecting compatible micrometers, calipers and other Digimatic gages to U-WAVE

		The second secon	5 5 5		
Gage		Assembled appearance	Connecting unit/connecting cable	Transmitter	Receiver
For digimatic	Standard	Front Back		U-WAVE-TM With buzzer 264-623	
micrometers	Dust/ water- proof	Front Back	02AZF310	U-WAVE-TM Dust/water-proof 264-622	
For calipers	Standard	Front Back	02AZF300	U-WAVE-TC With buzzer 264-621	Midayo
roi campers	Dust/ water- proof	IP 67 Front Back	02AZF310	U-WAVE-TC Dust/water-proof 264-620 U-WAVE (fit	U-WAVE-R 02AZD810D Design registered in Japan
Digimatic		155	Connecting Cable*	U-WAVE-T With buzzer 02AZD880G	Design registered in Japan
gages	7		cable*	U-WAVE-T Dust/water-proof 02AZD730G	

Note: Select according to the Digimatic gage to be connected. Refer to pages 24 and 25 for connecting cables.



Manage Measurement Data Centrally and Wirelessly on a Smartphone, Tablet or PC


Mitutoyo Bluetooth® U-WAVE fit

U-WAVE-TMB/TCB



More compact and thinner for a better fit with Digimatic gages, and featuring improved operability and performance inherited from its predecessor, U-WAVE-TMB/ TCB is now available with Bluetooth® wireless technology. No receiver is required, and one PC can connect up to seven units of Mitutoyo Bluetooth® U-WAVE fit. Dust /water-(IP) 67 proof models are also available for arduous shop floor usage.











Note: Connectivity of this application software and U-WAVE-TMB/TCB to every single Bluetooth® device is not guaranteed.

Major Advantages of Introducing Mitutoyo Bluetooth® U-WAVE fit



a Receiver

Measurement data can be ransmitted to PCs, tablets and nartphones without a receiver if



Cost Reduction Effect

System can be configured at reduced cost, just by connecting to an existing Digimatic gage.



Higher Efficiency

Data can be input by single button operation. Since there is no need for nual input misinput does not occu Efficiency is greatly improved



Data Management

Measurement data can be managed 'Visualization of quality" helps prevent the generation of defective products.

Easy Data Saving

phones and tablets independent of the measurement site.

You can use with confidence since it is labeled with the wireless certification number acquired in the country of purchase.





With Bluetooth® wireless technology for Easy Pairing with Your Digimatic Micrometer or Caliper

U-WAVE-TMB/ TCB is compatible with most Digimatic micrometers and calipers.

Refer to pages 28 to 42 for attachable digimatic gages




Digimatic micrometers



Digimatic calipers

Digimatic gage, connecting unit and transmitter combinations

		Assembled appearance	Connecting unit	Transmitter
For micrometers	Buzzer type		No.02AZF310	U-WAVE-TMB No.264-627
For micr	Dust/ water- proof type			U-WAVE-TMB No.264-626
For calipers	Buzzer type		No.02AZF300	U-WAVE-TCB No.264-625
For ca	Dust/ water- proof type	The state of the s	No.02AZF310	U-WAVE-TCB No.264-624 P67



Note1: We cannot guarantee the operation of this application and U-WAVE TMB/TCB with all Bluetooth equipped devices.

 $Note 2: Google\ Play\ and\ the\ Google\ Play\ logo\ are\ trademarks\ of\ Google\ LLC.\quad Apple\ and\ the\ Apple\ logo\ are\ trademarks\ of\ Apple\ lnc.$

* By enabling the direct input feature within U-WAVEPAK-BW the results can be written directly to Excel. The results do not include the transmitter device ID. Use of our optional USB-ITPAK or MeasurLink software allows for data sorting by individual transmitter IDs.

Measurement Navigation Application Mitutoyo U-WAVE Navi




Navigates your measurements easily and steadily

Mitutoyo *Bluetooth*[®] U-WAVE fit allows you to start measurements with your smartphone.




Images and text can be used to build a clear step by step measurement procedure. The app guides you how to measure and also shows you GO/NG judgment.



Easy data management



Data export to PC



Mitutoyo U-WAVE Navi is available at Google Play for free download.

Note: Google Play and the Google Play logo are trademarks of Google LLC.





MeasurLink

Achieve "Visualization of Quality"

Collecting the measurement data

Measurement Data Wireless Communication System

U-WAVE

IoT of Quality Control

Measurement Data Network System

MeasurLink

Configure the measurement network system MeasurLink using U-WAVE as a base



What is **MeasurLink**®?

MeasurLink is an IoT platform for quality management that realizes "Visualization of Quality" by enabling real-time data collection from the networked Digimatic gages and global control and analysis. U-WAVE supports MeasurLink as an infrastructure that collects and controls data.

Preventing defectives

Collects data from the Digimatic gages on the network and performs statistical process control (SPC) to warn of possible generation of defectives.


Diagnosis by data analysis

Checking measurement results by accessing the data base and performing various analyses helps investigate and resolve process performance concerns.

Simply start achieving IoT

In addition to conventional data storage, the network can be configured in steps to simply start IoT of Quality Control.

Linkage between U-WAVE and MeasurLink



Note: MeasurLink® is a registered trademark of Mitutoyo Corporation in Japan and Mitutoyo America Corporation in the United States



Specifications

Wireless Communication Specifications

Product name	Wireless communication	Wireless communication distance	Transmission output	Modulation method	Communication frequency	Used band
U-WAVE-T/TM/TC	Original (based on IEEE802.15.4)	Approx. 20 m (line of sight)	U-WAVE-T: 1 mW (0 dBm) or less U-WAVE-TC/TM: 2.5 mW (4 dBm) or less	DS-SS (Direct Sequence - Spread Spectrum) Resistant to interfering signals and noise	2.4 GHz band	15 channels (2.405 to 2.475 GHz at intervals of 5 MHz)
U-WAVE-TMB/TMC	Bluetooth® 4.2 Low Energy	Approx.16 m (line of sight) Approx. 10 m (on shop floor)	3.2 mW (5 dBm) or less (Class2)	FH-SS (Frequency-Hopping Spread Spectrum)	2.4 GHz band	in accordance with FH-SS (2.400~2.483GHz)

 $Note \ 1: This product is a radio \ equipment \ classified \ in \ the \ 2.4 \ GHz \ Wide-band \ Low \ Power \ Data \ Communication \ System.$

• Transmitter (Refer to pages 12 and 13 for combinations.)

Product name	Model	Order No.	Protection level	Data reception indication	Powersupply	Battery life	Mass	Appearance	External dimensions
U-WAVE-TM	Buzzer type	264-623	N/A	LED, buzzer		Approximately 400,000 transmissions	18 g	Mikutoyo Casanteni-rena Mar	Unit: mm
(for micrometers)	Dust/water-proof type	264-622	IP67	LED		in continuous use	18 g	Nitutoyo	12.9
U-WAVE-TMB	Buzzer type	264-627	N/A	LED, buzzer		Approximately 1 year under normal conditions of use,	18 g	Mitutoyo La demonstrative strate de	Unit: mm
(for micrometers)	Dust/water-proof type	264-626	IP67	LED		but varies according to usage.	18 g	Milutoyo La seeneral repair (g)	12.9
U-WAVE-TC	Buzzer type	264-621	N/A	LED, buzzer	Lithium battery CR2032×1	Approximately 400,000 transmissions in continuous use	18 g	Models of the second of the se	Unit: mm
(for calipers)	Dust/water-proof type	264-620	IP67	LED			18 g	Midopo	\$4 T
U-WAVE-TCB	Buzzer type	264-625	N/A	LED, buzzer		Approximately 1 year under normal conditions of use,	18 g	MELLOYD LI MANUFACTOR LE	Unit: mm
(for calipers)	Dust/water-proof type	264-624	IP67	LED		but varies according to usage.	18 g	Mildoyo	24.00
11 111115	Buzzer type	02AZD880G	N/A	LED, buzzer		Approximately	23 g	D. Miller C. Sept.	Unit: mm
U-WAVE-T	Dust/water-proof type	02AZD730G	IP67	LED		400,000 transmissions in continuous use	23 g	C Milding LL-WAVE-77	18.5

To use this product, conformity to the radio law of each country is required. Please contact your dealer or nearest Mitutoyo sales office.

Note 2: Not compatible with the conventional Mu-WAVE, for which communication specifications are different.



• Connecting unit (Refer to pages 12 and 13 for combinations.)

Product name	Model	Order No.	Protection level	Mass	Appearance	External dimensions
Commention weigh	For standard type	02AZF300	N/A	6 g		26.25 Unit: mm
Connecting unit	For dust/water-proof type	02AZF310	IP67	6 g		27.15 Unit: mm

• Receiver (Refer to pages 12 and 13 for combinations.)


Product name	Model	Order No.	Power supply	Connectable U-WAVE-R units	Connectable U-WAVE-T	Mass	Appearance	External dimensions		Standard accessory: U-WA	VEPAK software
Floudethame	Wouei	Order No.	rower suppry	(per PC)	units	IVIGSS	Appearance	External uninensions	System Environment: Compatible OS	Main specifications	Data format
U-WAVE-R	U-WAVE-R	02AZD810D	USB bus power system	Up to 15	Up to 100	130 g	MELEON U-WAVE-N	Unit: mm	Windows 2000 Professional (SP4 or later)* Windows XP Home Edition (SP2 or later)* Windows XP Professional (SP2 or later)* Windows Vista* Windows 7* Windows 8/8.1* Windows 10* Note: Windows 10 Mobile is not supported. * 32-bit, 64-bit OS supported <versions 10="" confirmed="" on="" operational="" windows=""> • U-WAVEPAK Ver.1.020 or later <connectability confirmed="" for="" pc="" tablet=""> • Microsoft Surface Pro 6 (the version whose operation on Windows10 Professional is confirmed) • Required environment: DVD drive (required for installation), USB port x2 ports or more</connectability></versions>	Setup of dedicated driver software (USB and virtual COM port) Initial setting of ID number and frequency selection (required only once for the first time) Load data to Microsoft Excel or Notepad through the data interface function	Header — DT1: Measurement data ST1: Status code ☆ Digimatic gage display value*1 U-WAVE-TC/TM/T ID: 00 to 99 U-WAVE-R ID: 00 to 99

Note: U-WAVEPAK software is packed together with the U-Wave receiver. If your computer has no DVD drive then please download and install U-WAVEPAK from our website.

• Dedicated cable for U-WAVE-T (Refer to pages 12 and 13 for combinations.)

		Connecting cable		Gage cor	nnectors on data cable		Digimatic ports on gage			
Product name	Connector type	Orde	er No.	Picture of gage	Data switch	Picture of Digimatic port	Applicable models			
	Connector type	Standard	For foot switch	connector	Dataswittii	Ficture of Digitilatic port	Applicable filodels			
	A Water-proof type with output button	02AZD790A	02AZE140A		✓		[Digimatic caliper] 500-712-20/500-713-20, etc. 550-301-20/550-331-20, etc. 552-302-10/552-303-10, etc. 552-155-10/552-156-10, etc. 552-181-10/552-182-10, etc.	[Digimatic special application caliper] 573-601-20/573-602-20, etc. [Digimatic depth gage] 571-251-20/571-252-20, etc. [Digimatic scale unit] 572-600, 572-601, etc.		
	B Water-proof type with output button	02AZD790B	02AZE140B	uns	✓		[Digimatic micrometer] 293-140-30/293-141-30, etc. 293-230-30 etc. 340-251-30/340-252-30 293-666-20/293-667-20, etc. 227-201-20/227-203-20, etc. 227-205-20/227-206-20, etc. 227-223-20 etc. [Dedicated micrometers for Digimatic] 422-230-30/422-231-30, etc. 406-250-30/406-251-30, etc. 343-250-30/343-251-30, etc. 369-250-30/369-251-30, etc.	345-250-30/345-251-30, etc. 314-251-30/314-252-30, etc. [Digimatic micrometer head] 350-251-30/350-261-30, etc. [Digimatic holtest] 468-161/468-162, etc. [Digimatic depth gage] 329-250-30/329-251-30, etc.		
	C Straight type with output button	02AZD790C	02AZE140C		✓		[Digimatic caliper] 500-150-30/500-151-30, etc. 500-500-10/500-501-10, etc. 500-443 etc. [Digimatic special application caliper] 573-718-20/573-719-20, etc. 573-716-20/573-717-20, etc. 573-191-30/573-291-30 573-181-30/573-182-30, etc. [Digimatic depth gage] 571-201-30/571-202-30, etc.	[Digimatic micrometer head] 164-163/164-164 [Digimatic scale unit] 572-203-10/572-213-10 572-300-10/572-301-10, etc.		
Dedicated cable for U-WAVE-T	D Flat 10-pin type	02AZD790D	02AZE140D		_		[Digimatic indicator] ID-H ID-F (Note)	[High-precision height gage] QM-Height		
	E Round 6-pin type	02AZD790E	02AZE140E		_		[Hardness testing machines] HM-100, HM-200, HV-100, HR-300/400/500, HH-411			
	F Flat straight type	02AZD790F	02AZE140F		_		[Digimatic indicator] ID-CX, ID-C (Peak-Value Hold Type), ID-C (Calculation type), ID-C (Bore Gage Type), ID-U (Note), ID-SS (Note), ID-SX (Note) [Digimatic height gage] 192-663-10/192-613-10/570-322/570-227, etc. (Flat L-shape, cable outlet is right) [ABS borematic] 568-361/568-362, etc. [Digimatic bore gage] 511-501/511-502, etc.	[Scale unit] 572-460/572-560/572-480-10/572-580-10, etc. [Hardness testing machines] HH-300 [Digimatic depth gage] Digimatic type (ID-CX)		
	G Flat straight water-proof type	02AZD790G	02AZE140G	4	_	O CONTRACTOR OF THE PARTY OF TH	[Digimatic indicator] ID-N, ID-B			

Note:If your digimatic gage doesn't have a DATA button, use the button on U-WAVE-T connection or connect it to a foot switch by using the optional foot switch connecting cable.



Mitutoyo

Optional Products

Application system

Product name	Model	Compatible OS: Windows*1	Compatible Excel version*2	Order No.
USB-ITPAK	06AFM386	2000 SP4 XP SP2 or later Vista 7 8 8.1	2002 2003 2007 2010 2013 2016 365	USB-ITPAK V2.1

^{*1 32-}bit, 64-bit OS supported Windows 10 Mobile is not supported. *2 The operation with Excel for MAC OS is not guaranteed.

UInstallation bracket Kit for U-WAVE-T

Product	Туре	Order No.	Application example	Attachable unit	Accessory
Bracket for U-WAVE-T	standard	02AZE200		U-WAVE-T	 Detachable fastener: 2pcs. (mirror imaged) Mounting screws for U-WAVE: 2 pcs.
Bracket for QM- Height	dedicated for QM-Height	02AZE990		U-WAVE-T	 Mounting screws for back plate: 2 pcs. Mounting screws for U-WAVE: 2 pcs.
Bracket for digimatic indicator	dedicated for ID-S and ID-C digimatic indicator	02AZF670		U-WAVE-TM/TMB	 Mounting screws for back plate: 2 pcs. Mounting screws for U-WAVE: 2 pcs.
Bracket for ID-N	dedicated for ABS coolant proof digimatic indicator ID-N	02AZF675		U-WAVE-TM/TMB	 Mounting screws for back plate: 2 pcs. Mounting screws for U-WAVE: 2 pcs.

• Application examples of the mounting plate (02AZE200)



Image of fastener attachment to main gage



QM-Height



ID-C







U-WAVE-TM/TMB compatible Digimatic micrometers/heads

* Current product

			* Current product
No.	Product name	Unit	Connecting unit
-10		mm	

			* Current produ
Order No.	Product name	Unit	Connecting unit
293-140			
*293-140-30			
293-141			
*293-141-30		mm	
293-142		"""	
*293-142-30			
293-143			
*293-143-30	QuantuMike		
293-180	Quantulvilke		
*293-180-30			
293-181			
*293-181-30		inch/mm	
293-182			
*293-182-30			
293-183			
*293-183-30			
293-230			
*293-230-30			
293-231			
*293-231-30			
293-232			
*293-232-30 293-233			02AZF310
*293-233-30			
293-234			
*293-234-30			
293-235			
*293-235-30			
293-236	-		
*293-236-30			
293-237			
*293-237-30			
293-238			
293-250			
293-250-10	Coolant proof micrometer	mm	
*293-250-30	Coolant proof inicrometer	"""	
293-251			
293-251-10			
*293-251-30			
293-252			
293-252-10			
*293-252-30			
293-253			
293-253-10			
*293-253-30 293-254			
293-254-10 *293-254-30	-		
293-255			
293-255-10	-		
*293-255-30	-		
293-256	-		
293-256-10	-		
*293-256-30	-		
233 230 30	I	I	<u> </u>

Oudou No	Dredust name	Unit	Connecting unit
Order No.	Product name	Unit	Connecting unit
293-257			
293-257-10		mm	
*293-257-30			
293-330			
*293-330-30			
293-331			
*293-331-30 293-332			
*293-332-30			
293-333			
*293-333-30			
293-334			
*293-334-30			
293-335			
*293-335-30			
293-336			
*293-336-30	-		
293-350	-		
293-350-10			
*293-350-30			
293-351			
293-351-10			02AZF310
*293-351-30		inch/mm	
293-352			
293-352-10			
*293-352-30			
293-353	Coolant proof micrometer		
293-353-10			
*293-353-30			
293-354			
293-354-10			
*293-354-30			
293-355			
293-355-10			
*293-355-30 293-356			
293-356-10			
*293-356-30			
293-357			
293-357-10			
*293-357-30			
293-960	-		
*293-960-30			
293-961			
*293-961-30			
293-962	1		
*293-962-30			
293-963			
*293-963-30		mm	
293-964		mm	
293-965			
293-966			
*293-966-30			

* Current product

Order No. Product name Unit Connecting up 314-251-10 *314-251-10 *314-251-30 314-252 314-252-10 *314-253-30 314-253-10 *314-253-30 314-261 314-261-10 *314-261-30 314-262-10 *314-262-30 314-351 314-351 314-351 314-352-30 314-352-30 314-352-30 314-352-30 314-352-30 314-352-30 314-353-30	init
314-251-10 *314-251-30 314-252 314-252-10 *314-253-30 314-253-30 314-253-10 *314-253-30 314-261 314-261-10 *314-261-30 314-262 314-262-10 *314-262-30 314-351-10 *314-351-10 *314-351-30 314-352 314-352-10 *314-352-30	
*314-251-30 314-252 314-252-10 *314-253 314-253 314-253 314-253-30 314-261 314-261-10 *314-261-30 314-262 314-262-10 *314-262-30 314-351 314-351 314-351 314-351-30 314-352 314-352-30	
314-252 314-252-10 *314-253-30 314-253 314-253-30 314-261 314-261-10 *314-262-30 314-262 314-262-30 *314-351 314-351-30 314-352 314-352-30	
314-252-10 *314-253-30 314-253-10 *314-253-30 314-261 314-261-10 *314-262-30 314-262-30 *314-262-30 314-351 314-351-30 314-352 314-352-30	
*314-252-30 314-253 314-253-10 *314-253-30 314-261 314-261-10 *314-261-30 314-262 314-262-10 *314-262-30 314-351 314-351-30 314-352 314-352-30 *314-352-30	
314-253 314-253-10 *314-253-30 314-261 314-261-10 *314-262-30 314-262-10 *314-262-30 314-351 314-351-10 *314-352 314-352 314-352-30	
314-253-10 *314-253-30 314-261 314-261-10 *314-262 314-262 314-262-10 *314-262-30 314-351 314-351-10 *314-351-30 314-352-30	
*314-253-30 314-261 314-261-10 *314-261-30 314-262 314-262-10 *314-262-30 314-351 314-351-10 *314-351-30 314-352 314-352-30	
314-261 314-261-10 *314-261-30 314-262 314-262-10 *314-262-30 314-351 314-351-10 *314-351-30 314-352 314-352-30	
314-261-10 *314-261-30 314-262 314-262-10 *314-262-30 314-351 314-351-10 *314-351-30 314-352 314-352-30	
*314-261-30 314-262 314-262-10 *314-262-30 314-351 314-351-10 *314-351-30 314-352 314-352-10 *314-352-30	
314-262 314-262-10 *314-262-30 314-351 314-351-10 *314-351-30 314-352 314-352-10 *314-352-30	
314-262-10 *314-262-30 314-351 314-351-10 *314-351-30 314-352 314-352-10 *314-352-30	
*314-262-30 314-351 314-351-10 *314-351-30 314-352 314-352 314-352-30	
314-351 314-351-10 *314-351-30 314-352 314-352-10 *314-352-30	
314-351 314-351-10 *314-351-30 314-352 314-352-10 *314-352-30	
*314-351-30 314-352 314-352-10 *314-352-30	
314-352 314-352-10 *314-352-30	
314-352-10 *314-352-30	
*314-352-30	
31/1-353	02AZF310
314-353-10 inch/mm	
*314-353-30	
314-361	
314-361-10	
*314-361-30 02AZF310	
314-362 344-363-40	
314-362-10 *314-362-30	
317-251	
*317-251-30	
317-252 mm	
*317-252-30	
317-351	
*317-351-30	
317-352 inch/mm	
*317-352-30	
323-250	
*323-250-30	
323-251	
*272.251.20	
323-252 Uni-micrometer mm	
*323-252-30	
323-253	
*323-253-30	
323-350	
*323-350-30	
323-351	
*323-351-30 inch/mm	
323-352	
*323-352-30	
323-353	
*323-353-30	

Order No.	Dread out was a	Unit	Connecting unit
	Product name	Unit	Connecting unit
324-251			
324-251-10			
*324-251-30			
324-252			
324-252-10 *324-252-30			
324-253		mm	
324-253-10			
*324-253-30			
324-254			
324-254-10			
*324-254-30			
324-351	Gear tooth micrometer		•
324-351-10			
*324-351-30			
324-352			
324-352-10			
*324-352-30		inch/mm	
324-353		IIICI/IIIII	
324-353-10			
*324-353-30			
324-354			
324-354-10			
*324-354-30			
326-251		mm	02AZF310
326-251-10			
*326-251-30			
326-252 326-252-10			
*326-252-30			
326-253			
326-253-10			
*326-253-30			
326-254			
326-254-10			
*326-254-30	6		
326-351	Screw thread micrometer		
326-351-10			
*326-351-30			
326-352			
326-352-10			
*326-352-30		inch/mm	
326-353			
326-353-10			
*326-353-30			
326-354			
326-354-10			
*326-354-30			
329-250 329-250-10			
*329-250-30			
329-251	Depth micrometer	mm	
329-251-10	Departimerometer		
*329-251-30			
329-350		inch/mm	
	I.		I

Product name Order No. Unit Connecting unit 329-350-10 *329-350-30 329-351 inch/mm Depth micrometer 329-351-10 *329-351-30 331-251 *331-251-30 331-252 *331-252-30 331-253 *331-253-30 331-254 *331-254-30 mm 331-261 *331-261-30 331-262 *331-262-30 331-263 *331-263-30 331-264 *331-264-30 Spline micrometer 331-351 *331-351-30 331-352 *331-352-30 331-353 *331-353-30 02AZF310 331-354 *331-354-30 inch/mm 331-361 *331-361-30 331-362 *331-362-30 331-363 *331-363-30 331-364 *331-364-30 340-251 340-251-10 *340-251-30 mm 340-252 340-252-10 *340-252-30 Outside micrometer 340-351 340-351-10 *340-351-30 inch/mm 340-352 340-352-10 *340-352-30 342-251 *342-251-30 342-252 Point micrometer mm *342-252-30 342-253

* Current product

			* Current product
Order No.	Product name	Unit	Connecting unit
*342-253-30			
342-254			
*342-254-30			
342-261		mm	
*342-261-30			
342-262	Point micrometer		
*342-262-30			
342-263			
*342-263-30			
342-264			
*342-264-30			
342-271	Crimp height micrometer		
*342-271-30	Criffip fielght fillerometer		
342-351			
*342-351-30			
342-352			
*342-352-30			
342-353			
*342-353-30			
342-354			02AZF310
*342-354-30	Point micrometer		
342-361	- Tome micrometer	inch/mm	
*342-361-30			
342-362			
*342-362-30			
342-363			
*342-363-30			
342-364			
*342-364-30		_	
342-371 *342-371-30	Crimp height micrometer		
343-250			
*343-250-30			
343-251			
*343-251-30			
343-252		mm	
*343-252-30	_		
343-253			
*343-253-30			
343-350	Caliper type outside micrometer		
*343-350-30			
343-351			
*343-351-30			
343-352		inch/mm	
*343-352-30			
343-353			
*343-353-30			
345-250			
345-250-10			
*345-250-30		mm	
345-251	Caliper type inside micrometer	mm	
345-251-10			
*345-251-30			
345-350		inch/mm	

Order No.	Product name	Unit	Connecting unit
345-350-10			
*345-350-30			
345-351	Caliper type inside micrometer	inch/mm	
345-351-10			
*345-351-30			
350-251			
350-251-10			
*350-251-30			
350-252			
350-252-10			
*350-252-30			
350-253			
350-253-10			
*350-253-30 350-254			
350-254-10			
*350-254-30			
350-261			
350-261-10			
*350-261-30			
350-271			
350-271-10			
*350-271-30			
350-272		mm	02AZF310
350-272-10			
350-272-20			
*350-272-30			
350-273			
350-273-10			
*350-273-30	Digimatic micrometer head		
350-274			
350-274-10			
350-274-20			
*350-274-30			
350-281			
350-281-10			
*350-281-30			
350-282 350-282-10			
*350-282-30			
350-283			
350-283-10			
*350-283-30			
350-284			
350-284-10			
*350-284-30			
350-351			
350-351-10			
*350-351-30			
350-352		inch/mm	
350-352-10		inch/mm	
*350-352-30			
350-353			
350-353-10			

* Current product

			* Current product
Order No.	Product name	Unit	Connecting unit
*350-353-30			
350-354			
350-354-10			
*350-354-30			
350-357-10			
*350-357-30			
350-361			
350-361-10			
*350-361-30			
350-381			
350-381-10	Digimatic micrometer head	inch/mm	
*350-381-30			
350-382			
350-382-10			
*350-382-30			
350-383			
350-383-10			
*350-383-30			
350-384 350-384-10			
*350-384-30			
369-250			
*369-250-30			
369-251			
*369-251-30			
369-252		mm	
*369-252-30			
369-253			02AZF310
*369-253-30			
369-350	Disk micrometer		
*369-350-30			
369-351			
*369-351-30		in als from	
369-352		inch/mm	
*369-352-30			
369-353			
*369-353-30			
389-251			
*389-251-30			
389-252			
*389-252-30			
389-261			
*389-261-30		mm	
389-262			
*389-262-30			
389-271	Sheet metal micrometer		
*389-271-30			
389-272			
*389-272-30			
389-351			
*389-351-30		in ah Inn ra	
389-352		inch/mm	
*389-352-30			
389-361			

Product name Order No. Unit Connecting unit *389-361-30 389-362 *389-362-30 inch/mm 389-371 Sheet metal micrometer *389-371-30 389-372 *389-372-30 395-251 *395-251-30 395-252 *395-252-30 395-253 *395-253-30 395-254 *395-254-30 395-261 *395-261-30 395-262 *395-262-30 mm 395-263 *395-263-30 395-264 *395-264-30 395-271 *395-271-30 395-272 02AZF310 *395-272-30 395-273 *395-273-30 395-274 Tube micrometer *395-274-30 395-351 *395-351-30 395-352 *395-352-30 395-353 *395-353-30 395-354 *395-354-30 395-362 *395-362-30 395-363 inch/mm *395-363-30 395-364 *395-364-30 395-371 *395-371-30 395-372 *395-372-30 395-373 *395-373-30 395-374 *395-374-30

* Current product

			Current product
Order No.	Product name	Unit	Connecting unit
406-250			
*406-250-30			
406-251			
*406-251-30		mana	
406-252		mm	
*406-252-30			
406-253			
*406-253-30	Outside missemeter, non-retating spindle		
406-350	Outside micrometer, non-rotating spindle		
*406-350-30			
406-351			
*406-351-30		inch/mm	
406-352		IIICI/IIIII	
*406-352-30			
406-353			
*406-353-30			
422-230			
*422-230-30			
422-231			02AZF310
*422-231-30			
422-232		mm	
*422-232-30			
422-233			
*422-233-30			
422-260			
*422-260-30			
422-261			
*422-261-30			
422-270			
*422-270-30	-		
422-271			
*422-271-30	District of the second of the		
422-330	Blade micrometer, non-rotating spindle		
*422-330-30			
422-331			
*422-331-30	_		
422-332			
*422-332-30			
422-333			
*422-333-30		inch/mm	
422-360 *433-360-30	-	IIICI/IIIII	
*422-360-30	-		
422-361	_		
*422-361-30	-		
422-370	-		
*422-370-30	-		
422-371			
*422-371-30			



U-WAVE-TC/TCB compatible Digimatic caliper/depth gage

	_		
*	Current	t produc	t

			* Current product
Order No.	Product name	Unit	Connecting unit
500-150-20			
*500-150-30			
500-151-20			
*500-151-30			
500-152-20			
*500-152-30			
500-153			
*500-153-30			
500-154-20 *500-154-30			
500-155-20			
*500-155-30		mm	
500-156-20			
*500-156-30			
500-157-20			
*500-157-30			
500-158-20			
*500-158-30			
500-161-21			
*500-161-30			
500-162-21			
*500-162-30			
500-167			
*500-167-30			
500-168			
*500-168-30			
500-170-20	ABS Digimatic caliper		02AZF300
*500-170-30	,		
500-171-20			
*500-171-30 500-172-20			
*500-172-30			
500-172-30			
*500-173-30		inch/mm	
500-174-20			
*500-174-30			
500-175-20			
*500-175-30			
500-176-20			
*500-176-30			
500-177-20			
*500-177-30			
500-178-20			
*500-178-30			
500-201-21		mm	
*500-201-30			
500-202-21 *500-202-20		inch/mm	
*500-202-30 500-203-21			
*500-203-21 *500-203-30		mm	
500-204-21			
*500-204-30		inch/mm	
500-205			
*500-205-30		mm	
300 200 50	1	I .	I

Order No.	Product name	Unit	Connecting unit
500-233-21			
*500-233-30			
500-234-21			
*500-234-30			
500-235-21			
*500-235-30		mm	
500-236-21	ABS Digimatic caliper		
*500-236-30	- 122 2.9		
500-443			
500-444			
500-445			
500-463 500-464		inch/mm	
500-465		incn/mm	
571-201-20			
*571-201-30			02AZF300
571-202-20			
*571-202-30		mm	
571-203-20	-		
*571-203-30			
571-211-20	Depth gage		
*571-211-30			
571-212-20		:	
*571-212-30		inch/mm	
571-213-10			
*571-213-30			
573-191-20		mm	
*573-191-30	ABS low force caliper	111111	
573-291-20	Abb low force camper	inch/mm	
*573-291-30			
500-712-10		mm	02AZF310
*500-712-20			
500-713-10 *F00-713-20			
*500-713-20 500-714-10			
*500-714-10			
500-716-11			
*500-716-20			
500-717-11			
*500-717-20	-		
500-718-11			
*500-718-20			
500-719-10	ABS coolant proof caliper		
*500-719-20			
500-720-11		inch/mm	
*500-720-20		IIICI/IIIII	
500-721-10			
*500-721-20			
500-722-10			
*500-722-20		mm	
500-723-10			
*500-723-20			
500-724-10			
*500-724-20			

*571-263-20

			* Current product
Order No.	Product name	Unit	Connecting unit
500-727-11			
*500-727-20		mm	
500-728-11		mm	
*500-728-20			
500-735-10			
500-735-20			
500-736-10	-		
*500-736-20			
500-737-10 *500-737-20			
500-737-20	ABS coolant proof caliper		
*500-738-20			
500-762-10	_	inch/mm	
*500-762-20			
500-763-10			
*500-763-20			
500-764-10			
*500-764-20			
500-769-10	-		
*500-769-20			
550-301-10		mm	
*550-301-20 550-311-10			
*550-311-20		inch/mm	
550-331-10	ABS Digimatic caliper, nib style jaws		
*550-331-20		mm	
550-341-10		inch/mm	02AZF310
*550-341-20		IIICI/IIIII	UZAZF31U
551-301-10		mm	
*551-301-20			
551-311-10		inch/mm	
*551-311-20 551-331-10	ABS Digimatic caliper, nib style and standard jaws		
*551-331-20		mm	
551-341-10			
*551-341-20		inch/mm	
571-100-20	Tine treed double some		
*571-200-20	Tire tread depth gage	mm	
571-251-10			
*571-251-20			
571-252-10			
*571-252-20			
571-253-10 *571-253-20			
571-254-10			
*571-254-20			
571-255-10	Depth gage		
*571-255-20			
571-261-10			
*571-261-20			
571-262-10		inch/mm	
*571-262-20			
571-263-10			

* Current product

			* Current product
Order No.	Product name	Unit	Connecting unit
571-264-10			
*571-264-20		inch/mm	
571-265-10	Depth gage	inch/mm	
*571-265-20			
571-301-10			
*571-301-20		mm	
571-302-10			
*571-302-20			
571-311-10			
571-311-20		inch/mm	
571-312-10			
*571-312-20			
573-601			
*573-601-20			
573-602			
*573-602-20			
573-604			
*573-604-20			
573-605			
*573-605-20			
573-606			
*573-606-20			
573-608			02AZF310
*573-608-20			
573-611		mm	
*573-611-20 573-612			
*573-612-20			
573-614			
*573-614-20			
573-615			
*573-615-20	_		
573-616	_		
*573-616-20	Dedicated caliper		
*573-618			
*573-618-20	-		
573-621			
*573-621-20	1		
573-622	1		
*573-622-20			
573-625			
*573-625-20			
573-626			
*573-626-20			
573-634			
*573-634-20			
573-635			
*573-635-20			
573-645			
*573-645-20			
573-646			
*573-646-20			
573-647			
*573-647-20			

Order No.	Product name	Unit	Connecting unit
573-648			
*573-648-20			
573-651			
*573-651-20			
573-652			
*573-652-20			
573-653			
*573-653-20			
573-654			
*573-654-20			
573-661		mm	
573-661-20			
573-662			
*573-662-20			
573-676			
*573-676-20			
573-677			
*573-677-20			
573-679			
*573-679-20			
573-701			
*573-701-20			02AZF310
573-702			
*573-702-20	Dedicated caliper		
573-704	Dedicated Caliper		
*573-704-20			
573-705			
*573-705-20			
573-706			
*573-706-20			
573-708			
*573-708-20		inch/mm	
573-721			
*573-721-20			
573-725			
*573-725-20			
573-734			
*573-734-20 573-745			
*573-745-20			
573-746			
*573-746-20			
573-740-20			
*573-751-20			
573-752			
*573-752-20			
573-761			
*573-761-20			
373-101-20	1	I	I